

MS Greenline

Simple, fast and effective cleaning



MS Schippers

Passion for Farming

Cleaning and disinfecting is important for maintaining an optimal living environment for your animals. When eliminating pathogens, it is very important to clean thoroughly before disinfecting. It is a time consuming job but extremely important for your animals' welfare.

The MS Greenline gets the job done!

MS Greenline

The MS Greenline is an aid for thorough cleaning and disinfecting/decontaminating your housing. When combined with a high pressure system, it allows you to clean, apply foam and disinfect/decontaminate in one run.

Always the correct concentration of the appropriate product

**Safe operation period.
No contact with products**

With one easy operation, you can switch between rinsing, foaming or disinfecting

The MS Greenline is made of Stainless Steel and it is easy to connect to existing high pressure systems.



Pathogen pressure in the housing

Immediately after emptying

After pressure washing

After cleaning

After disinfection



50.000.000
pathogens/cm²

20.000.000
pathogens/cm²

100.000
pathogens/cm²

<500
pathogens/cm²

Immediately after emptying

Spray clean with cold water

Spray clean with MS Topfoam

Disinfect with MS Megades Novo

Step-by-step plan for hygienic cleaning:

- 1 Thorough preparation.** Remove all materials and equipment (manure, drinkers, feeders, etc.) from the housing unit.
- 2 Coat** all surfaces in the housing unit (and associated materials) with MS Topfoam. In cases of heavy soiling, pre-rinse the surfaces.
- 3 Spray** the housing unit (and all associated materials) clean using a high-pressure washer and then rinse with low-pressure water.
- 4 Disinfect** the housing unit with MS Megades Novo, to kill all remaining microorganisms.
- 5 Rinse** the housing unit (and all associated materials) with clean water and allow it to dry.
- 6 A low-pathogen environment.** The housing unit is ready for use again.

MS Greenline

is available in three models.



MS Greenline mobile 2.0

- In one act possible to switch from rinsing to foaming or disinfecting
- Connect to existing high pressure systems
- Space for 2 jugs of ± 30 kg

Comes with:

- 1x hose (3/8" male thread) by 3 meters to connect MS Greenline and the high-pressure system
- 1x foam lance (1/4" male thread)
- 2x stainless steel suction lance
- 1x suction blue
- 1x suction yellow

MS Greenline wall mounting 2.0

- In one act possible to switch from rinsing to foaming or disinfecting
- Connect to existing high pressure systems
- Space for 2 jugs of ± 30 kg

Comes with:

- 1x hose (3/8" male thread) by 3 meters to connect MS Greenline and the high-pressure system
- 1x foam lance (1/4" male thread)
- 2x stainless steel suction lance
- 1x suction blue
- 1x suction yellow

MS Greenline mini

- Rinse and foam in one
- Easy to connect to existing high pressure systems
- Connection for 1 jug

Comes with:

- 1x hose (3/8" male thread) by 3 meters to connect
- MS Greenline Mini and the high-pressure system
- 1x foam lance (1/4" male thread)
- 1x stainless steel suction lance
- 1x suction blue
-
-

MS Schippers
Passion for Farming

Schippers Export BV

Rond Deel 12
5531, AH Bladel (NL)
T: 0031-(0)497-339774
F: 0031-(0)497-339779
export@msschippers.com
www.msschippers.com

Schippers Canada Ltd

660 Maitland Street
London, ON, N5Y 2V8
Phone 1866-995-7771
Fax 1866-995-7772
info@schippers.ca
www.schippers.ca

Schippers UK Ltd

235 Old Marylebone Road
London, NW1 5QT
Tel: 01733-592022
Fax: 01733-370968
info@msschippers.co.uk
www.msschippers.co.uk