## Boss with "Soft Flow Technology"

Soft Flow Technology provides the answer; creating that constant output application rate throughout your treatment process, unlike Hand Pump Applicators. Our Soft Flow rates of application provide the gentle flow needed to treat cracks and cervices in all types of structures where insects live. Match Soft Flow to your spray tip of choice and experience a day's work without Hand Pumping. You will never go back.

The Boss Battery Technology is something you can count on.

PRO-128 – 32	20 – 512 - 1024SFT	PRO-1024 (HIGH VOLUME)
Approximate values and flow settings:		Approximate values and flow settings:
Run Times – continuous use		Run Times – continuous use
Low Flow – 4 hours + 60 PSI Closed Trigger		Low Flow – 1.5 hours 80 PSI Closed Trigger
High Flow – 1.5 hours 70 PSI Closed Trigger		High Flow – 1 hour 85 PSI Closed Trigger
Low Flow Setting and Tips		Low Flow Setting
1 -	00mls/min 14oz 20mls/min 21oz	Pro-1024 Pin and Cone Spray Tip PDS-2.5MM 2700mls/min 112oz
Pin and Cone Spray Tip		
<u> </u>	00mls/min 17oz 35mls/min 8oz	High Flow Setting
High Flow Setting and Tips		Pro-1024 Pin and Cone Spray Tip PDS-2.5MM 3300mls/min 91oz
Pin and Cone Spray Tip Tip 08 Pin/Cone 1	800mls/min 60oz	
Fan Spray Tip Tip 8002 9	20mls/min 32oz	
High Density Proximity Tips (Sold Separately) Low Flow Only		
High Density Proximity Tip – 1.5 HPD-M1.5 100mls/min 3.4oz High Density Proximity Tip – 3 HDP-M3 220mls/min 7.4oz		